

TECHNICAL DESCRIPTION OF FIBER OPTIC CABLE

1. Cable construction

A-DQ(ZN)4Y-(1-8)x12-200-652D/657A1-1036b	
8	
3	
4	
5	
6	
7	
	A-DQ(ZN)4Y-(1-8)x12-200-652D/657A1-1036b

Cable construction

1. Outer sheath: PA

2. Optical loose tube: 1,4mm PBT Tube

3. Intramodule compound: Thixotropic compound

4. Optical Fiber: 200 mkm Single-mode Fiber according to ITU-T G.652.D and G.657.A1

5. Central strength element: Glass reinforced plastic 2,3mm FRP-E

6. Rip-cord: Water-swellable yarn

7. Water-blocking element of core: Water-swellable yarn

8. Core filler: PE

Temperature ranges	Storage and transportation	Installation	Operating			
	temperature	temperature	temperature			
	from -40 to +60 °C	from -10 to +50 °C	from -40 to +60 °C			
Resistance to water	Water resistant					
penetration						
Relative humidity at +35° C, %		98				
Outer diameter, mm		6,0±0,2				
Average weight of 1 km of the		33±5%				
cable, kg						

2. Mechanical characteristics

Calculated tensile strength, not less than ¹ , kN Dynamic	2,0
Minimum bending radius	20D
Short-term crush test, kN/cm (N/10cm)	0,05 (500)
Resistance to axial torsion at angle ±360° on 2m length cable	Resistant
Resistance to bends at angle $\pm 90^{\circ}$ with a radius equal to 20 nominal cable diameters	Resistant
Resistance to impact 2 J	Resistant

-

 $^{^{\}rm 1}$ Tensile strength value is for maximum number of fibers design



3. Packaging and marking

Cable factory length, km	6
Package	Drum №10 (1001x655x1001)
Tolerance, %	±3,0
Short lengths (customer approval)	Maximum 5%
Marking method	Inkjet printing
The accuracy of marking, %	±0,5

4. Coloring

Coloring of fibers in loose tube (According to Customer's requirements color can be different).											
1	2	3	4	5	6	7	8	9	10	11	12
red	green	blue	yellow	white	slate	brown	violet	aqua	black	orange	pink

Coloring of optical loose tube (According to Customer's requirements color can be different). Core-filler color is natural. 2 3 4 5 6 7 8 1 yellow white violet red green blue slate brown

5. Product data

Fiber count	24	48	72	96
Loose tubes x fibers	2x12	4x12	6x12	8x12